



## Power saw blade for Kasto, Ko-Bi3, Length L / TPI: 450/4



### Order data

Order number	171650 450/4
GTIN	4045197347053
Item class	16E

### Description

#### Version:

**KOMET bi-metal** – tooth tips of HSS-M3 and blade body of spring steel. For high cutting performance and feed rates. Unbreakable for maximum safety at the workplace.

#### Note:

**Especially for Kasto machines** (clamping holes offset from 38 mm blade width).

**Important:** The instructions included with the saw blades must be followed in all details.

**KOMET HSS saw blades:** Other versions such as VP 7 (7° rake angle, Vario tothing) and P 13 (13° rake angle – especially for stainless steels) available on request on short delivery times.

Tooth type: normal

Width: 38 mm

Thickness: 2 mm

Clamping hole Ø: 8.5 mm

### Technical description

Width	38 mm
Thickness	2 mm
Clamping hole Ø	8.5 mm
TPI	4
Length L	450 mm
Tooth type	normal
Tool material	Ko-Bi3
Type of product	Power saw blade

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1100 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions		
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Uni	suitable		
wet maximum	suitable		