



Power saw blade for Kasto, Ko-Bi3, Length L / TPI: 450/6



Order data

Order number	171650 450/6
GTIN	4045197347060
Item class	16E

Description

Version:

KOMET bi-metal – tooth tips of HSS-M3 and blade body of spring steel. For high cutting performance and feed rates. Unbreakable for maximum safety at the workplace.

Note:

Especially for Kasto machines (clamping holes offset from 38 mm blade width).

Important: The instructions included with the saw blades must be followed in all details.

KOMET HSS saw blades: Other versions such as VP 7 (7° rake angle, Vario tothing) and P 13 (13° rake angle – especially for stainless steels) available on request on short delivery times.

Tooth type: normal

Width: 38 mm

Thickness: 2 mm

Clamping hole Ø: 8.5 mm

Technical description

Length L	450 mm
Width	38 mm
Thickness	2 mm
Clamping hole Ø	8.5 mm
TPI	6
Tooth type	normal
Tool material	Ko-Bi3
Type of product	Power saw blade

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1100 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Uni	suitable		
wet maximum	suitable		