

Garant
DIN counterbore for through holes, uncoated, Counterbore \varnothing D1 x pin \varnothing D2: 26X17mm

Order data

Order number	156120 26X17
GTIN	4045197087874
Item class	11M

Description
Version:

Spiral fluted counterbore. The pilot \varnothing matches the intended purpose:

f – for through holes **fine** quality to DIN ISO 273.

m for through holes **medium** quality to DIN ISO 273.

Application:

For counterboring socket head screws DIN 912, 6912, 7984, and cheese head screws ISO 1207 (DIN 84).

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Technical description

Number of cutting edges Z	3
for screw size	M16
Feed f in steel < 500 N/mm ²	0.2 mm/rev.
Pin \varnothing	17 mm
Counterbore \varnothing	26 mm
for quality of the hole	f
Pre-drill \varnothing	17 mm
Overall length L	192 mm
Morse taper MT	3

Step height L ₁ 1st step with chamfer	35 mm
Point angle	180 degrees
Coating	uncoated
Tool material	HSS
Standard	Manufacturer's standard
Shank	Morse taper
Through-coolant	no
Type of product	Counterbore

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable	33 m/min	N
Steel < 500 N/mm ²	suitable	28 m/min	P
Steel < 750 N/mm ²	suitable	27 m/min	P
wet maximum	suitable		