

Flat magnet with internal thread, Ferrite, Ø: 40mm



Order data

Order number	085915 40
GTIN	2050000965296
Item class	08Q

Description

Version:

- **Shielded flat magnet made of hard ferrite with insert nut.**
- **Galvanised surface.**
- **Temperature-resistant up to maximum 120 °C.**

Application:

For clamping, assembling, incorporation by screw fastening.

Note:

Screw-in hooks with external thread under No. 085921.

Technical description

Height	8 mm
Height with thread	18 mm
Weight	60 g
Material of the surface	galvanised
Nominal clamping force	125 N
Ø	40 mm
Thread	M5 mm
Threaded socket	yes
maximum temperature resistance	120 °C

Material of the magnet core	Ferrite
Type of product	Flat gripper magnet

Accessories

Screw-in hook set with external thread 10 pieces Thread M5	085921 M5
--	-----------