

Garant

Power saw blade for Kasto, HSS, Length L / TPI: 350/10



Order data

Order number	171150 350/10
GTIN	4045197095169
Item class	11R

Description

Version:

GARANT – saw blade made of molybdenum alloyed high performance cutting steel **HSS (DMo5)**. Due to constantly high hardness and extreme toughness, particularly **high cutting performances** are obtained (reduced cutting times and longer tool life). The precise set ensures a straight cut.

Note:

Especially for Kasto machines (clamping holes offset from 38 mm blade width).

Important: The instructions included with the saw blades must be followed in all details.

Tooth type: normal

Width: 32 mm

Thickness: 2 mm

Clamping hole Ø: 8.5 mm

Technical description

Clamping hole Ø	8.5 mm
Length L	350 mm
Width	32 mm
Thickness	2 mm
TPI	10
Tooth type	normal
Tool material	HSS
Type of product	Power saw blade

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable only under restricted conditions		
wet maximum	suitable		