

## Garant

### Power saw blade for Kasto, HSS, Length L / TPI: 550/6



#### Order data

Order number	171150 550/6
GTIN	4045197095268
Item class	11R

#### Description

##### Version:

**GARANT** – saw blade made of molybdenum alloyed high performance cutting steel **HSS (DMo5)**. Due to constantly high hardness and extreme toughness, particularly **high cutting performances** are obtained (reduced cutting times and longer tool life). The precise set ensures a straight cut.

##### Note:

**Especially for Kasto machines** (clamping holes offset from 38 mm blade width).

**Important:** The instructions included with the saw blades must be followed in all details.

Tooth type: normal

Width: 45 mm

Thickness: 2.25 mm

Clamping hole Ø: 10.5 mm

#### Technical description

TPI	6
Thickness	2.25 mm
Clamping hole Ø	10.5 mm
Width	45 mm
Length L	550 mm
Tooth type	normal
Tool material	HSS
Type of product	Power saw blade

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions		
wet maximum	suitable		