

Garant

Power saw blade for Kasto, HSS, Length L / TPI: 700/6



Order data

Order number	171150 700/6
GTIN	4045197095367
Item class	11R

Description

Version:

GARANT – saw blade made of molybdenum alloyed high performance cutting steel **HSS (DMo5)**. Due to constantly high hardness and extreme toughness, particularly **high cutting performances** are obtained (reduced cutting times and longer tool life). The precise set ensures a straight cut.

Note:

Especially for Kasto machines (clamping holes offset from 38 mm blade width).

Important: The instructions included with the saw blades must be followed in all details.

Tooth type: normal

Width: 50 mm

Thickness: 2.5 mm

Clamping hole Ø: 10.5 mm

Technical description

Width	50 mm
Clamping hole Ø	10.5 mm
TPI	6
Length L	700 mm
Thickness	2.5 mm
Tooth type	normal
Tool material	HSS
Type of product	Power saw blade

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable only under restricted conditions		
wet maximum	suitable		