

bimos

Neon swivel work chair, PU foam, with castors, low, Colour: ORANGE**Order data**

Order number	965432 ORANGE
GTIN	4016849498256
Item class	96J

Description**Version:**

Neon swivel work chair with interchangeable cushion system. The cushion elements are simply mounted and fixed with a click. With ergonomic adjustment options: Synchronous technology with weight adjustment, seat height adjustment using gas pressure safety spring, seat angle adjustment, seat depth adjustment, backrest height adjustment. With flexible band running all around the edge in different colours.

Seat and backrest of soft PU foam. Easy-care, washable, robust and resistant to weak acids and alkalis as well as mechanical impacts.

Standard:**DIN 68877****Optional extras:**

Pair of multi-function armrests No. 965455.

Technical description

Armrest pair can be adjusted	yes
Height adjustment version	Gas pressure spring

Synchro mechanism	yes
Base version	Set of castors
Type of height adjustment	Height adjustment lever
Lumbar support (spinal discs)	no
Colour of seat material	black
Support frame version	5-point star base
Series	Neon
Material of seat surface	PU foam
Backrest height	570 mm
Seat depth adjustment range	420 - 480 mm
Standard	DIN 68877
Seat tilt adjustment	yes
Seat width	470 mm
Roller version	Load-responsive castor braking for hard floors.
Continuous contact backrest adjustment	no
Material of backrest	PU foam
Material of base	Aluminium matt powder coated
Colour of the strap	orange
Version	with castors
Load capacity chair	120 kg
Height adjustment range	450 mm
Type of product	Swivel work chair