

bimos

**Neon swivel work chair, synthetic leather, with castors, low, Colour: GREY****Order data**

Order number	965438 GREY
GTIN	4016849501765
Item class	96J

**Description****Version:**

Neon swivel work chair with interchangeable cushion system. The cushion elements are simply mounted and fixed with a click. With ergonomic adjustment options: Synchronous technology with weight adjustment, seat height adjustment using gas pressure safety spring, seat angle adjustment, seat depth adjustment, backrest height adjustment. With flexible band running all around the edge in different colours.

Seat and backrest with synthetic leather cladding, comfortable and soft. Washable and easy-care, resistant to oils and disinfectants.

**Standard:****DIN 68877****Optional extras:**

Pair of multi-function armrests No. 965455.

**Technical description**

Seat width	470 mm
Synchro mechanism	yes

Colour of seat material	black
Base version	Set of castors
Backrest height	570 mm
Continuous contact backrest adjustment	no
Armrest pair can be adjusted	yes
Type of height adjustment	Height adjustment lever
Standard	DIN 68877
Material of base	Aluminium matt powder coated
Series	Neon
Roller version	Load-responsive castor braking for hard floors.
Material of seat surface	Synthetic leather
Lumbar support	yes
Seat depth adjustment range	420 - 480 mm
Support frame version	5-point star base
Height adjustment version	Gas pressure spring
Colour of the strap	grey
Load capacity chair	120 kg
Height adjustment range	450 mm
Type of product	Swivel work chair