

bimos

Neon swivel work chair, PU foam, with castors, low, Colour: GREY**Order data**

Order number	965432 GREY
GTIN	4016849518312
Item class	96J

Description**Version:**

Neon swivel work chair with interchangeable cushion system. The cushion elements are simply mounted and fixed with a click. With ergonomic adjustment options: Synchronous technology with weight adjustment, seat height adjustment using gas pressure safety spring, seat angle adjustment, seat depth adjustment, backrest height adjustment. With flexible band running all around the edge in different colours.

Seat and backrest of soft PU foam. Easy-care, washable, robust and resistant to weak acids and alkalis as well as mechanical impacts.

Standard:**DIN 68877****Optional extras:**

Pair of multi-function armrests No. 965455.

Technical description

Seat width	470 mm
Standard	DIN 68877

Material of backrest	PU foam
Series	Neon
Lumbar support (spinal discs)	no
Backrest height	570 mm
Material of base	Aluminium matt powder coated
Roller version	Load-responsive castor braking for hard floors.
Support frame version	5-point star base
Height adjustment version	Gas pressure spring
Type of height adjustment	Height adjustment lever
Seat depth adjustment range	420 - 480 mm
Seat tilt adjustment	yes
Colour of seat material	black
Material of seat surface	PU foam
Armrest pair can be adjusted	yes
Continuous contact backrest adjustment	no
Base version	Set of castors
Synchro mechanism	yes
Colour of the strap	grey
Load capacity chair	120 kg
Height adjustment range	450 mm
Type of product	Swivel work chair