

bimos

**Neon swivel work chair, fabric, with castors, low, Colour: GREY****Order data**

Order number	965444 GREY
GTIN	4016849529875
Item class	96J

**Description****Version:**

Neon swivel work chair with interchangeable cushion system. The cushion elements are simply mounted and fixed with a click. With ergonomic adjustment options: Synchronous technology with weight adjustment, seat height adjustment using gas pressure safety spring, seat angle adjustment, seat depth adjustment, backrest height adjustment. With flexible band running all around the edge in different colours.

Seat and backrest with soft fabric upholstery. Comfortable, hard-wearing and breathable.

**Standard:****DIN 68877****Optional extras:**

Pair of multi-function armrests No. 965455.

**Technical description**

Base version	Set of castors
Continuous contact backrest adjustment	no
Lumbar support	yes

Colour of seat material	black
Backrest height	570 mm
Roller version	Load-responsive castor braking for hard floors.
Support frame version	5-point star base
Height adjustment version	Gas pressure spring
Standard	DIN 68877
Armrest pair can be adjusted	yes
Series	Neon
Type of height adjustment	Height adjustment lever
Seat width	470 mm
Seat depth adjustment range	420 - 480 mm
Material of base	Aluminium matt powder coated
Material of seat surface	Fabric
Synchro mechanism	yes
Colour of the strap	grey
Load capacity chair	120 kg
Height adjustment range	450 mm
Type of product	Swivel work chair