

bimos

**Neon swivel work chair, Supertec, with castors, low, Colour: GREY****Order data**

Order number	965450 GREY
GTIN	4016849508900
Item class	96J

**Description****Version:**

Neon swivel work chair with interchangeable cushion system. The cushion elements are simply mounted and fixed with a click. With ergonomic adjustment options: Synchronous technology with weight adjustment, seat height adjustment using gas pressure safety spring, seat angle adjustment, seat depth adjustment, backrest height adjustment. With flexible band running all around the edge in different colours.

Supertec is comfortable, soft, breathable, extremely tough, easy to clean and non-slip. Thanks to its micro reinforcement, this material combines the advantages of fabric and PU foam.

**Standard:****DIN 68877****Optional extras:**

Pair of multi-function armrests No. 965455.

**Technical description**

Roller version	Load-responsive castor braking for hard floors.
Type of height adjustment	Height adjustment lever

Continuous contact backrest adjustment	no
Synchro mechanism	yes
Lumbar support	yes
Standard	DIN 68877
Material of base	Aluminium matt powder coated
Support frame version	5-point star base
Backrest height	570 mm
Series	Neon
Base version	Set of castors
Seat width	470 mm
Height adjustment version	Gas pressure spring
Material of seat surface	Supertec
Seat depth adjustment range	420 - 480 mm
Colour of seat material	black
Armrest pair can be adjusted	yes
Colour of the strap	grey
Load capacity chair	120 kg
Height adjustment range	450 mm
Type of product	Swivel work chair