



## Grooving toolholder, right-hand, Shank size: 25mm



### Order data

Order number	278015 25
GTIN	4062406381394
Item class	22B

### Description

#### Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm). For grooving inserts No. 278029 – 278036.

### Technical description

Grooving depth $t_{max}$	21 mm
Head length $L_1$	39 mm
Screw	279816 4 (SW5; 5 Nm)
Overall length $L$	129 mm
Functional width $L_4$	25 mm
Groove width $w$	3 mm
Groove width $w$	4 mm
Shank size	25 mm
Application type	right-hand
Through-coolant	no
axial grooving possible	no
Type of product	Clamp toolholder

