



eco-grooving toolholder, left-hand, Shank size: 20mm

Order data

Order number	278016 20
GTIN	4062406381714
Item class	22B

Description
Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm). For grooving inserts No. 278029 – 278036.

Technical description

Shank size	20 mm
Grooving depth t_{max}	21 mm
Functional width L_4	20 mm
Head length L_1	39 mm
Overall length L	129 mm
Screw	279816 4 (SW5; 5 Nm)
Groove width w	3 mm
Groove width w	4 mm
Application type	left-hand
Through-coolant	yes
axial grooving possible	no
Type of product	Clamp toolholder

