



Grooving toolholder, right-hand, Shank size: 20mm



Order data

Order number	278015 20
GTIN	4062406381387
Item class	22B

Description

Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm). For grooving inserts No. 278029 – 278036.

Technical description

Head length L_1	39 mm
Functional width L_4	20 mm
Shank size	20 mm
Overall length L	129 mm
Groove width w	3 mm
Groove width w	4 mm
Screw	279816 4 (SW5; 5 Nm)
Grooving depth t_{max}	21 mm
Application type	right-hand
Through-coolant	no
axial grooving possible	no
Type of product	Clamp toolholder

