



Grooving toolholder, right-hand, Shank size: 16mm



Order data

Order number	278017 16
GTIN	4062406381738
Item class	22B

Description

Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm). For grooving inserts No. 278029 – 278036.

Technical description

Shank size	16 mm
Functional width L_4	16 mm
Overall length L	100 mm
Head length L_1	30 mm
Screw	279816 3 (SW5; 5 Nm)
Groove width w	3 mm
Groove width w	4 mm
Grooving depth t_{max}	12 mm
Application type	right-hand
Through-coolant	yes
axial grooving possible	no
Type of product	Boring bar

