



## Grooving toolholder, right-hand, Shank size: 20mm



### Order data

Order number	278017 20
GTIN	4062406381745
Item class	22B

### Description

#### Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm). For grooving inserts No. 278029 – 278036.

### Technical description

Grooving depth $t_{\max}$	12 mm
Shank size	20 mm
Screw	279816 4 (SW5; 5 Nm)
Head length $L_1$	30 mm
Functional width $L_4$	20 mm
Overall length $L$	120 mm
Groove width $w$	3 mm
Groove width $w$	4 mm
Application type	right-hand
Through-coolant	yes
axial grooving possible	no
Type of product	Boring bar

