




Grooving toolholder, left-hand, Shank size: 20mm



Order data

Order number	278018 20
GTIN	4062406381776
Item class	22B

Description

Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm). For grooving inserts No. 278029 – 278036.

Technical description

Head length L_1	30 mm
Shank size	20 mm
Overall length L	120 mm
Grooving depth t_{max}	12 mm
Screw	279816 4 (SW5; 5 Nm)
Functional width L_4	20 mm
Groove width w	3 mm
Groove width w	4 mm
Application type	left-hand
Through-coolant	yes
axial grooving possible	no
Type of product	Boring bar

