



Grooving toolholder, right-hand, Shank size: 25mm



Order data

Order number	278017 25
GTIN	4062406381752
Item class	22B

Description

Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm). For grooving inserts No. 278029 – 278036.

Technical description

Overall length L	120 mm
Groove width w	3 mm
Groove width w	4 mm
Functional width L ₄	25 mm
Screw	279816 4 (SW5; 5 Nm)
Grooving depth t _{max}	12 mm
Head length L ₁	30 mm
Shank size	25 mm
Application type	right-hand
Through-coolant	yes
axial grooving possible	no
Type of product	Boring bar

