



Boring bar for grooving, right-hand, Shank \varnothing DS: 20mm



Order data

| | |
|--------------|---------------|
| Order number | 278023 20 |
| GTIN | 4062406381639 |
| Item class | 22B |

Description

Version:

All sizes with just one insert seat for two groove widths (3 mm and 4 mm). For grooving inserts No. 278029 – 278036.

Technical description

| | |
|--|--------------------------|
| Minimum pre-drill $\varnothing D_{\min}$ | 16.5 mm |
| t_{\max} internal machining | 5 mm |
| Overall length L | 200 mm |
| Groove width w | 3; 4 mm |
| Screw | 279816 5 (TX20; 5 Nm) |
| Centre offset L_3 | 8 mm |
| Overhang L_1 recessed holders | 30 mm |
| Shank $\varnothing D_s$ | 20 mm |
| Application range | radial internal grooving |
| Application type | right-hand |
| Through-coolant | yes |
| axial grooving possible | yes |
| Type of product | Boring bar |

