



## Dynafile® pneumatic belt linisher, Type: 15006



### Order data

Order number	079551 15006
GTIN	616026150065
Item class	03R

### Description

#### Version:

Versatile machines with **adjustable linishing belt guides, exactly true-running belts**, and with an exchangeable **contact arm** allowing the use of contact wheel or side face. The composite linishing belt coating enables **quick** and **easy change of the linishing belt**. The **linishing belt** cooling via the exhaust air prolongs the working life of the belts. Adjustable handle **Mini-Dynafile® II set**, handy linisher in compact and flexible lightweight design. Adjustable linishing head. Ideal for working in restricted places. Linishing belt dimensions 3 - 4, 6, 13x305 mm.

#### Application:

For abrading, deburring, blending, finishing and polishing, ideal also for flexible access to difficult places.

#### Supplied with:

Including the necessary coupling adaptors. **Mini-Dynafile® II**, 3 contact arms, set of linishing belts, carrying case.

#### Note:

Other contact arm versions for Dynafile® from No. 079559 available on request or in our eShop.

### Technical description

Weight	0.8 kg
Model range	Mini- Dynafile II
Operating noise	81 dB(A)
Tape width	3-4; 6; 13; mm
Band length	305 mm

Output power	295 W
maximum speed	25000 min <sup>-1</sup>
maximum air consumption	564 l/min
Manufacturer's designation	Mini-Dynaflex II set
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Compressed air connection	1/4 in
Connection thread	NPT
Packaging	Carrying case
Type of product	Finishing machine

---

## Accessories

Contact arm for Mini-Dynaflex® II Type 15026	079562 15026
Contact arm for Mini-Dynaflex® II Type 15030	079562 15030
Contact arm for Mini-Dynaflex® II Type 15028	079562 15028