

**Garant****Radial Heavy-Duty blade carrier, right-hand, Insert size: 10mm****Order data**

Order number	260616 10
GTIN	4062406383183
Item class	21U

**Description****Version:**

Modular copy turning tool for cutting depths up to 70 mm.

**Application:**

In conjunction with GARANT Heavy-Duty toolholder (No. 274004).

**Attention:**

Without clamping screws (these are supplied with the toolholders).

**Technical description**

Shim	269005 11
Pack of insert screws	269028 1
suitable indexable insert	RC.X 1003
Insert size	10 mm
Shim screw	269013 2
maximum cutting depth $t_{max}$	60 mm
Overall length $L_{tot}$	142 mm
Application type	right-hand
Type of product	Cartridges

## Accessories

Set of insert screws Type 1	269028 1
Shim Type 11	269005 11