


Garant**Radial Heavy-Duty blade carrier, left-hand, Insert size: 10mm****Order data**

Order number	260617 10
GTIN	4062406384319
Item class	21U

Description**Version:**

Modular copy turning tool for cutting depths up to 70 mm.

Application:

In conjunction with GARANT Heavy-Duty toolholder (No. 274004).

Attention:

Without clamping screws (these are supplied with the toolholders).

Technical description

Insert size	10 mm
maximum cutting depth t_{max}	60 mm
Pack of insert screws	269028 1
suitable indexable insert	RC.X 1003
Shim	269005 11
Shim screw	269013 2
Overall length L_{tot}	142 mm
Application type	left-hand
Type of product	Cartridges

Accessories

Shim Type 11	269005 11
Set of insert screws Type 1	269028 1