



Power saw blade for Kasto, Ko-Bi3, Length L / TPI: 650/6



Order data

| | |
|--------------|---------------|
| Order number | 171650 650/6 |
| GTIN | 4045197347138 |
| Item class | 16E |

Description

Version:

KOMET bi-metal – tooth tips of HSS-M3 and blade body of spring steel. For high cutting performance and feed rates. Unbreakable for maximum safety at the workplace.

Note:

Especially for Kasto machines (clamping holes offset from 38 mm blade width).

Important: The instructions included with the saw blades must be followed in all details.

KOMET HSS saw blades: Other versions such as VP 7 (7° rake angle, Vario toothing) and P 13 (13° rake angle – especially for stainless steels) available on request on short delivery times.

Tooth type: normal

Width: 50 mm

Thickness: 2.5 mm

Clamping hole Ø: 10.5 mm

Technical description

| | |
|-----------------|-----------------|
| TPI | 6 |
| Thickness | 2.5 mm |
| Clamping hole Ø | 10.5 mm |
| Length L | 650 mm |
| Width | 50 mm |
| Tooth type | normal |
| Tool material | Ko-Bi3 |
| Type of product | Power saw blade |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | | |
| Alu > 10% Si | suitable only under restricted conditions | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1100 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | | |
| INOX < 900 N/mm ² | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Uni | suitable | | |
| wet maximum | suitable | | |