



Boring bar set, steel, with IC, right-hand, Type: SET07



Order data

Order number	260390 SET07
GTIN	4062406386191
Item class	29W

Technical description

Clamping height L_2	9 mm
Clamping height L_2	11 mm
Head length L_1	22.5 mm
Head length L_1	27.5 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
ISO code toolholder	A0810H SDUCR07
ISO code toolholder	A1012K SDUCR07
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Neck width L_4	8 mm

Neck width L_4	10 mm
Overall length L	100 mm
Overall length L	125 mm
Centre offset L_3	6.5 mm
Centre offset L_3	9 mm
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Type of product	Boring bar