



## Boring bar set, steel, with IC, right-hand, Type: SET06



### Order data

Order number	260390 SET06
GTIN	4062406386207
Item class	29W

### Technical description

Overall length L	100 mm
Overall length L	110 mm
Overall length L	125 mm
Head length L <sub>1</sub>	22 mm
Head length L <sub>1</sub>	27 mm
Head length L <sub>1</sub>	33 mm
Clamping height L <sub>2</sub>	7 mm
Clamping height L <sub>2</sub>	9 mm
Clamping height L <sub>2</sub>	11 mm
Centre offset L <sub>3</sub>	4 mm
Centre offset L <sub>3</sub>	6 mm

Centre offset L <sub>3</sub>	7 mm
Minimum pre-drill Ø D <sub>min</sub>	8 mm
Minimum pre-drill Ø D <sub>min</sub>	11 mm
Minimum pre-drill Ø D <sub>min</sub>	13 mm
Neck width L <sub>4</sub>	6 mm
Neck width L <sub>4</sub>	8 mm
Neck width L <sub>4</sub>	10 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	A0810J SCLCR06
ISO code toolholder	A1012K SCLCR06
ISO code toolholder	A0608H SCLCR06
Pack of insert screws	269028 7
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Type of product	Boring bar