

Garant GRIDLINE

Set of troughs, 20×24G, Drawer front height / type: 50/3



Order data

Order number	950460 50/3
GTIN	4062406388829
Item class	9GB

Description

Version:

Troughs and divider plates of plastic. Troughs slotted on the inside for division using divider plates.

Dividing material fills a complete drawer 20×24G.

Suitable for:

Drawers 20×24G.

Content:

Troughs 1K height 25 mm No. 951415: 8 pcs. size 6×6/4; 4 pcs. size 6×6/2; 4 pcs. size 2×6/1

Troughs divider plates (10 pcs.) No. 951275: 1 pc. size A; 3 pcs. size C

Technical description

suitable for drawers usable width in G	20
suitable for drawer front height	50 mm
suitable for drawer front height	100 mm
suitable for drawer front height	75 mm
suitable for drawer front height	150 mm
suitable for drawer front height	125 mm
suitable for drawer front height	250 mm
suitable for drawer front height	200 mm

suitable for drawer front height	300 mm
suitable for drawers usable width	500 mm
Material	Plastic
Drawer usable area in G	20×24
suitable for drawers usable depth	600 mm
Trough height	25 mm
suitable for drawers usable depth in G	24
suitable from drawer front height	≥ 50 mm
Width in G	20
Depth	600 mm
Width	500 mm
Height	25 mm
Depth in G	24
Weight	1.321 kg
Product name attribute	20×24G
Type of product	Drawer trough

Accessories

Trough divider platesSet 10 pieces Type C	951275 C
Trough height 25 mm1K Width×depth in G / type 6X6/2	951415 6X6/2
Trough height 25 mm1K Width×depth in G / type 2X6/1	951415 2X6/1
Trough divider platesSet 10 pieces Type A	951275 A
Trough height 25 mm1K Width×depth in G / type 6X6/4	951415 6X6/4