



## Band saw blade RRR Plus, 30 m, width mm / TPI: 6/6H



### Order data

Order number	172000 6/6H
GTIN	4045197253293
Item class	16F

### Description

#### Version:

**Regular tooth pitch** –Constant pitch with **0° rake angle** in plastic dispenser, no welded joint.

**RRR-Plus** made of alloyed tool steel, 30 m each coil.

#### Application:

Particularly suitable for smaller and medium size cross sections (up to maximum 70 mm contact length).

#### Note:

- **Regular pitch teeth 10°: Sizes 6/4H, 6/6H, 10/4H, 10/6H, 13/4H, 13/6H, 16/4H.**
- **Variable pitch teeth 0°: Size 6/1014, 10/1014, 13/1014.**

Tooth type: normal

Rake: 10 °

Tooth type: normal

Rake: 10 °

Thickness: 0.65 mm

### Technical description

Width	6 mm
-------	------

Rake	10°
Thickness	0.65 mm
Tooth type	normal
Product name attribute	30 m
Length	30 m
Type of product	Metal band saw blade

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	85 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	65 m/min	P
GG(G)	suitable	40 m/min	K
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		