

Garant
"4 in 1" drilling and turning tool 1.5×D, left-hand, Ø DC: 25mm

Order data

Order number	268405 25
GTIN	4062406392611
Item class	21X

Description
Version:

Plain shank.

Application:

1. Facing of end faces.
2. Drilling (drilling out and drilling from solid) – flat drilled hole end.
3. Internal longitudinal turning.
4. External longitudinal turning.

Note:

- **Choose corner radii and toolholder size as large as possible.**
- **Drilling tolerance + 0.15 mm (for drilling processes with a driven tool).**
- **When drilling greater than nominal Ø, residual material will remain.**
- **Always use internal cooling for drilling (at least 5 bar).**

Technical description

Reach L ₁	37.5 mm
Nominal Ø D	25 mm
Shank Ø D _s	32 mm
Pack of insert screws	269028 45 (IP20; 5 Nm)
suitable indexable insert	ZCMX 13..
Overall length L	180 mm
Application type	left-hand
Through-coolant	yes

Type of product

Boring bar

Accessories

Set of insert screws Type 43

269028 43

Set of insert screws Type 45

269028 45