

Garant**Carbide-tipped multi-purpose drills, Drill Ø: 4mm****Order data**

Order number	787070 4
GTIN	4062406390853
Item class	71C

Description**Version:**

Multi-purpose drill with **especially sharp carbide insert** for precise holes in different materials. Large-volume helical flute for **quick removal of dust and chips**. Shank of annealed special steel.

Application:

For drilling various materials, including in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass.**
- **Metal and material combinations in a single operation, such as when fitting windows or when reinforcing concrete.**

Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Technical description

Drill Ø	4 mm
overall length	75 mm
Flute length	40 mm
Tool material	Carbide
Use with impact / without impact	not for impact drilling
Shank	Plain shank
Type of product	Multi-purpose drill

