

Garant
Carbide-tipped multi-purpose drill set, Number of drills: 7

Order data

Order number	787078 7
GTIN	4062406393311
Item class	71C

Description
Version:

Multi-purpose drill with **especially sharp carbide insert** for precise holes in different materials. Large-volume helical flute for **quick removal of dust and chips**. Shank of annealed special steel.

Application:

For drilling various materials, including in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass.**
- **Metal and material combinations in a single operation, such as when fitting windows or when reinforcing concrete.**

Content:

Drill No. 787070: 1 pc. each size 4; 5; 6; 6; 8; 8; 10

Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Technical description

Number of drills	7
Drill Ø	4 - 10 mm
Tool material	Carbide

Use with impact / without impact	not for impact drilling
Shank	Plain shank
Type of product	Multi-purpose drill

Accessories

Carbide-tipped multi-purpose drills Drill Ø 6 mm	787070 6
Carbide-tipped multi-purpose drills Drill Ø 4 mm	787070 4
Carbide-tipped multi-purpose drills Drill Ø 10 mm	787070 10
Carbide-tipped multi-purpose drills Drill Ø 8 mm	787070 8
Carbide-tipped multi-purpose drills Drill Ø 5 mm	787070 5