

Garant

Carbide-tipped multi-purpose drills, Drill Ø: 12mm



Order data

| | |
|--------------|---------------|
| Order number | 787070 12 |
| GTIN | 4062406390907 |
| Item class | 71C |

Description

Version:

Multi-purpose drill with **especially sharp carbide insert** for precise holes in different materials. Large-volume helical flute for **quick removal of dust and chips**. Shank of annealed special steel.

Application:

For drilling various materials, including in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass.**
- **Metal and material combinations in a single operation, such as when fitting windows or when reinforcing concrete.**

Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Technical description

| | |
|----------------------------------|-------------------------|
| overall length | 150 mm |
| Flute length | 85 mm |
| Drill Ø | 12 mm |
| Tool material | Carbide |
| Use with impact / without impact | not for impact drilling |
| Shank | Plain shank |
| Type of product | Multi-purpose drill |

