



Pneumatic random orbital sander, Type: 58436



Order data

Order number	079656 58436
GTIN	616026584365
Item class	03R

Description

Version:

Powerful random orbital sanders with polyurethane hook and loop fastening backing pads. **Easy to use** due to light-weight composite housing and ergonomic hand application area. **Robust, smooth-running, and low-vibration pneumatic drive** with steel cylinder, low noise level. Dynorbital spirit orbital sander (152 mm) for central extraction. **Combination sander**, permits **orbital** abrasion for **coarse and intermediate sanding**, with a 5 mm stroke combined with **rotary** movement for high rates of material removal. Connection for **external suction**.

Supplied with:

Including the necessary coupling adaptors.

Note:

See No. 567775 or 567901 for hook and loop grinding discs.

DynaMaze hook and loop backing pad for No. 079655 and 079656 size X61V and size 58436 can be found under No. 567872 size 150.

Technical description

Weight	1.3 kg
Type of extraction	External
Manufacturer's designation	DynaLocke 152 mm

Backing pad Ø	150 mm
maximum speed	12000 min ⁻¹
maximum vibration to EN	2.67 m/s ²
maximum air consumption	654 l/min
Operating noise	82 dB(A)
Stroke	5 mm
Type of product	Orbital sander

Accessories

Paper velour-backed abrasive disc (A)6 + 1 holes Grit 320	567775 320
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 400	567775 400
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 80	567775 80
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 800	567775 800
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 60	567775 60
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 600	567775 600
PU hook and loop backing padDynaMaze External Ø 150 mm	567872 150
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 240	567775 240
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 120	567775 120
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 180	567775 180
Paper velour-backed abrasive disc (A)6 + 1 holes Grit 40	567775 40