

## ALLURIS

**Pull-tester FMT-W30, Measuring range: 500N****Order data**

Order number	478998 500
GTIN	4260244681144
Item class	47F

**Description****Version:**

- **Manual pull-tester with manual lever for determining the tensile strength of all non-soldered (crimped) cable connections.**
- **Space-saving, non-slip and sturdy bench-top device with hardened non-scratch base plate.**
- **Cordless, so always ready for use.**
- **Interchangeable mounting adapters with 12 different slot widths cover all popular sizes of cable.**

**Application:**

Testing cable connections to IEC, DIN, EN, BS, UL, SAE, MIL and NASA standards.

**Supplied with:**

Pull-tester complete with test adapter and terminal pull-off jig, USB interface and instruction manual.

**Optional extras:**

Various exchangeable adapters available, FMT\_W\_Connect evaluation software.

**Technical description**

Width	160 mm
Length	350 mm

Measuring range	500 N
Resolution	0.5 N
Height	75 mm
Slot width test adaptor	0.5 / 0.8 / 1.0 / 1.3 / 1.5 / 2.0 / 2.5 / 3.0 / 3.5 / 4.0 / 5.0 / 6.0 mm
Accuracy	±0.5 % (±1/2 digit)
Type of product	Draw bar pulling force gauge