

ALLURIS

Pull-tester FMT-W30, Measuring range: 1000N**Order data**

Order number	478998 1000
GTIN	4260244681151
Item class	47F

Description**Version:**

- **Manual pull-tester with manual lever for determining the tensile strength of all non-soldered (crimped) cable connections.**
- **Space-saving, non-slip and sturdy bench-top device with hardened non-scratch base plate.**
- **Cordless, so always ready for use.**
- **Interchangeable mounting adapters with 12 different slot widths cover all popular sizes of cable.**

Application:

Testing cable connections to IEC, DIN, EN, BS, UL, SAE, MIL and NASA standards.

Supplied with:

Pull-tester complete with test adapter and terminal pull-off jig, USB interface and instruction manual.

Optional extras:

Various exchangeable adapters available, FMT_W_Connect evaluation software.

Technical description

Width	160 mm
Measuring range	1000 N

Height	75 mm
Resolution	1 N
Length	350 mm
Slot width test adaptor	0.5 / 0.8 / 1.0 / 1.3 / 1.5 / 2.0 / 2.5 / 3.0 / 3.5 / 4.0 / 5.0 / 6.0 mm
Accuracy	±0.5 % (±1/2 digit)
Type of product	Draw bar pulling force gauge