



Modular counterboring set in a wooden stand, Size / shank size: 1/12



Order data

Order number	156700 1/12
GTIN	4033591011601
Item class	16C

Description

Version:

Set of holders, counterbores, and pilots for machining the most common bore \emptyset .

Application:

For DIN counterbores, as well as appropriate pilot / counterbore combinations for stepped holes or non-standard counterbores.

Content:

1× each counterbore No. 156730: 14.5; 16.5; 18.5; 20.5; 22.5; 24.5

1× each pilot No. 156750: 7; 7.5; 8; 8.5; 9; 9.5; 10; 10.5; 11; 11.5; 12; 13; 14; 15

1× each holder No. 156720 with shank: \emptyset 12 mm

Note:

Modular counterboring sets also available in HSS with optional TIN coating and brazed-on carbide tips with form "T" ISO inserts.

Through-coolant: yes

Number of cutting edges Z: 3

Number of cutting edges Z: 3

Counterbore range: 14.5 - 24.5 mm

Technical description

Counterbore range	14.5 - 24.5 mm
-------------------	----------------

Number of cutting edges Z	3
Tool material	HSS
Through-coolant	yes
Type of product	Counterbore