



## Knurl forming tool universal, Shank size: 10mm



### Order data

Order number	290010 10
GTIN	4030741657832
Item class	29H

### Description

#### Version:

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

**Modular design: Can be used as a right-hand or left-hand version.**

### Technical description

Shank height	10 mm
for knurl $\varnothing d_1$	10 mm
for knurl width w	4 mm
for knurl bore $\varnothing d_2$	4 mm
Working range	3 - 25 mm
Roller pin	299910 5
Shank width	10 mm
Cutting direction	left-hand and right-hand
for knurl profile	RBR 2×BL
for knurl profile	RAA 2×AA
for knurl profile	RBL 2×BR
for knurl profile	RGE30° BL/BR30°

for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool

---

## Accessories

Carbide roller pin Carbide Type 5	299910 5
-----------------------------------	----------