



Knurl forming tool right-hand, Shank size: 10mm



Order data

| | |
|--------------|---------------|
| Order number | 290018 10 |
| GTIN | 4030741660603 |
| Item class | 29H |

Description

Version:

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

- **Minimal pressure reduces stress on the workpiece and machine.**
- **Synchronising spindle for easy adjustment of knurl carriers and centre heights.**

Technical description

| | |
|----------------------------------|-----------------|
| Shank height | 10 mm |
| for knurl bore $\varnothing d_2$ | 4 mm |
| Working range | 0 - 15 mm |
| Roller pin | 299910 6 |
| for knurl $\varnothing d_1$ | 15 mm |
| for knurl width w | 4 mm |
| Shank width | 10 mm |
| for knurl profile | RAA 2×AA |
| for knurl profile | RBL 2×BR |
| for knurl profile | RGE45° BL/BR45° |
| for knurl profile | RAA 1×AA |

| | |
|-------------------|------------------------------|
| for knurl profile | RBR 2×BL |
| Type of product | Self-centering knurling tool |