



Knurl forming tool right-hand, Shank size: 10mm



Order data

Order number	290080 10
GTIN	4030741660924
Item class	29H

Description

Version:

Grub screws in the shank for clearance angle correction.
Carbide roller pin for increased wear resistance.

Top face of the shank = tip height

Technical description

for knurl bore $\varnothing d_2$	6 mm
Shank width	10 mm
for knurled countersunk $\varnothing d_3$	11 mm
Disc	299927 1
Closure stud	299925 1
for knurl width w	6 mm
Working range	3 - 50 mm
for knurl $\varnothing d_1$	15 mm
Shank height	10 mm
for knurl profile	RAA 1×AA
Type of product	Self-centering knurling tool

Accessories

Disc Type 1	299927 1
Closure stud Type 1	299925 1