



## Cut knurling tool universal, Shank size: 10mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 290210 10     |
| GTIN         | 4030741409486 |
| Item class   | 29H           |

### Description

#### Version:

**Modular design: Can be used universally as right-hand or left-hand version.**

Carbide running sleeve for increased wear resistance.

Quick tool adjustment by using the adjustment spindle.

#### Advantage:

- **Low vibration.**
- **Adjustment scale and synchronous adjustment spindle for adjusting the workpiece  $\varnothing$ .**
- **Reduced set-up times leading to reduced unit costs.**
- **Clearance angle correction of the knurls.**
- **Increased wear resistance due to specially hardened surface.**
- **For higher feed rates and cutting speeds.**

### Technical description

|                                   |           |
|-----------------------------------|-----------|
| Shank height                      | 10 mm     |
| Shank width                       | 10 mm     |
| for knurl $\varnothing d_1$       | 15 mm     |
| Carbide sleeve, cover disc, screw | 299920 5  |
| for knurl width w                 | 4 mm      |
| Working range                     | 3 - 50 mm |
| for knurl bore $\varnothing d_2$  | 8 mm      |

|                   |                              |
|-------------------|------------------------------|
| Cutting direction | left-hand and right-hand     |
| for knurl profile | RGE30° 2×AA                  |
| for knurl profile | RGE45° BL/BR15°              |
| Type of product   | Self-centering knurling tool |

---

## Accessories

Spare parts kit (3 pieces), carbide bush, cover washer,  
screw Type 5

299920 5