



## ECO knurl forming tool universal, Shank size: 16mm



### Order data

Order number	290036 16
GTIN	4030741881152
Item class	29H

### Description

#### Version:

Used conventionally.

#### Note:

Tip height must be adjusted.

### Technical description

Working range	3 - 50 mm
Roller pin	299911 6
for knurl width w	4 mm
for knurl $\varnothing d_1$	10; 15 mm
Shank height	16 mm
Shank width	16 mm
for knurl bore $\varnothing d_2$	4 mm
Cutting direction	left-hand and right-hand
for knurl profile	RBR 1×BL
for knurl profile	RBL 1×BR
for knurl profile	RBL 1×BR
for knurl profile	RGE30° 1×GV30°
for knurl profile	RBR 1×BL

Type of product

Self-centering knurling tool

---

## Accessories

HSS roller pinHSS Type 1

299911 1