



## ECO knurl forming tool universal, Shank size: 16Xmm



### Order data

Order number	290036 16X
GTIN	4030741007880
Item class	29H

### Description

#### Version:

Used conventionally.

#### Note:

Tip height must be adjusted.

### Technical description

Shank width	16 mm
Shank height	16 mm
for knurl $\varnothing d_1$	20; 25 mm
Working range	8 - 200 mm
for knurl bore $\varnothing d_2$	6 mm
for knurl width w	8 mm
Roller pin	299911 1
Cutting direction	left-hand and right-hand
for knurl profile	RBR 1×BL
for knurl profile	RBL 1×BR
for knurl profile	RBL 1×BR
for knurl profile	RGE30° 1×GV30°
for knurl profile	RBR 1×BL

Type of product

Self-centering knurling tool

---

**Accessories**

HSS roller pinHSS Type 1

299911 1

ECO knurl forming tool set Type 16

290050 16