



ECO knurl forming tool right-hand, Shank size: 16mm



Order data

Order number	290039 16
GTIN	4030741881176
Item class	29H

Description

Version:

Used conventionally.

Note:

Tip height must be adjusted.

Technical description

for knurl $\varnothing d_1$	15 mm
Working range	6 - 60 mm
Shank width	16 mm
for knurl width w	4 mm
Roller pin	299911 4
for knurl bore $\varnothing d_2$	4 mm
Shank height	16 mm
for knurl profile	RBL 2×BR
for knurl profile	RGE45° BL/BR45°
for knurl profile	RBR 2×BL
for knurl profile	RAA 1×AA

for knurl profile

RGE45° BL/BR45°

Type of product

Self-centering knurling tool