



## ECO knurl forming tool universal, Shank size: 20mm



### Order data

Order number	290041 20
GTIN	4030741707025
Item class	29H

### Description

#### Version:

Used conventionally.

**Can be used universally as right-hand or left-hand version.**

#### Note:

Tip height must be adjusted.

### Technical description

Roller pin	299911 3
Working range	10 - 110 mm
for knurl width w	8 mm
Shank height	20 mm
Shank width	20 mm
for knurl bore $\varnothing d_2$	6 mm
for knurl $\varnothing d_1$	20 mm
Cutting direction	left-hand and right-hand
for knurl profile	RBR 2×BL
for knurl profile	RBL 2×BR
for knurl profile	RAA 2×AA

for knurl profile	RAA 1×AA
for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool

---

## Accessories

ECO knurl forming tool set Type 20	290050 20
------------------------------------	-----------