

Garant**Electronics side cutter for ferrous materials, kW, overall length: 135mm**

Order data

Order number	726742 135
GTIN	4062406395032
Item class	71B

Description

Version:

Professional diagonal side cutter with slightly shearing cut. Both cutter parts are very accurately put together using carefully machined holes and polished surfaces to ensure a precise cut. With opening spring and ergonomically designed handles for secure and comfortable use. **2-component grips** of dissipative material. **Suitable for ESD work.**

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

Technical description

Cutter length	8 mm
overall length	135 mm
Head width	13.5 mm
Cutting capacity copper wire up to Ø	2 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	Carbon steel (C70)
Surface	phosphated, non-reflecting
Product name attribute	kW
with return spring	yes

Type of product

Cutting pliers