

Garant**Electronics side cutter clean cut, stronger jaws, kW, overall length: 135mm****Order data**

Order number	726702 135
GTIN	4062406395018
Item class	71B

Description**Version:**

Professional diagonal side cutter with slightly shearing cut. Both cutter parts are very accurately put together using carefully machined holes and polished surfaces to ensure a precise cut. With opening spring and ergonomically designed handles for secure and comfortable use. **2-component grips** of dissipative material. **Suitable for ESD work.**

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

Technical description

Cutter length	8 mm
Cutting capacity copper wire up to Ø	1.3 mm
Head width	13.5 mm
overall length	135 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	Carbon steel (C70)
Surface	phosphated, non-reflecting
Product name attribute	kW
with return spring	yes

Type of product

Cutting pliers