

**Garant**
**Electronics side cutter especially for hard wire, kW, overall length: 135mm**


## Order data

Order number	726762 135
GTIN	4062406395049
Item class	71B

## Description

### Version:

Professional diagonal side cutter with slightly shearing cut. Both cutter parts are very accurately put together using carefully machined holes and polished surfaces to ensure a precise cut. With opening spring and ergonomically designed handles for secure and comfortable use. **2-component grips** of dissipative material. **Suitable for ESD work.**

### Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

## Technical description

Head width	13 mm
Cutter length	12 mm
Cutting capacity copper wire up to Ø	1.3 mm
Cutting capacity hard wire up to Ø	0.4 mm
overall length	135 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	Carbon steel (C70)
Surface	phosphated, non-reflecting
Product name attribute	kW

with return spring	yes
Type of product	Cutting pliers