

**Garant****Electronics IC cutter, SFW, overall length: 130mm****Order data**

Order number	726942 130
GTIN	4062406395063
Item class	71B

**Description****Version:**

Professional cutters with slightly shearing cut. Both cutter parts are very accurately put together using carefully machined holes and polished surfaces to ensure a precise cut. With opening spring and ergonomically designed handles for secure and comfortable use. **2-component grips** of dissipative material. **Suitable for ESD work.**

**Material:**

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

**Technical description**

Cutting capacity copper wire up to Ø	1.02 mm
Head width	14 mm
Head length	18 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	very fine bevel
Material	Carbon steel (C70)
Surface	phosphated, non-reflecting
Product name attribute	SFW
Type of product	Cutting pliers

