

Garant**Electronics needle-nose pliers 48° angled, overall length: 150mm****Order data**

Order number	727182 150
GTIN	4062406395094
Item class	71B

Description**Version:**

The jaws of the cutter are accurately put together using carefully machined holes and polished surfaces. With opening spring and ergonomically designed handles for secure and comfortable use. **2-component** conductive grips, **suitable for ESDs**.

Needle-nose, serrated internal jaws.

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

Technical description

overall length	150 mm
Head width	13 mm
Jaw length	35 mm
electrostatic characteristic	EGB/ESD
Jaw design	angled
Type of jaws	Snipe-nose, serrated internal jaws
Handle	2-component grip
Material	Carbon steel (C70)
Surface	phosphated, non-reflecting
with return spring	yes

Type of product

Snipe nose pliers