

**Garant**
**Boring bar carbide, right-hand, Shank  $\varnothing$  / insert size: 25/16mm**

**Order data**

Order number	261112 25/16
GTIN	4062406398033
Item class	21T

**Technical description**

ISO code toolholder	E25S SVJBR/L 16
Pack of insert screws	269028 8
Head length $L_1$	44 mm
Minimum pre-drill $\varnothing D_{\min}$	28 mm
Clamping height $L_2$	24 mm
Neck width $L_4$	16.5 mm
Insert size	16 mm
suitable indexable insert	VB.. 1604..
Overall length L	250 mm
Setting angle $\kappa$	142 degrees
Centre offset $L_3$	4.6 mm
Shank $\varnothing D_s$	25 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 8	269028 8
-----------------------------	----------